



RENTAL SYSTEMS

24-HOUR HOTLINE 1300 130 750



760 KW VARIABLE SPEED WATER COOLED SCREW CHILLER

Unit Arrangement - Dimensions are Approximate

GENERAL DESCRIPTION AND FEATURES

- Ready for operation with minimal setup
- Carrier Smart Service remote monitoring.
- Single point power connection
- Variable Speed Technology
- BacNET/IP control connection
- Hot Gas By-Pass for low load operation

EQUIPMENT DATA

Model(s) 30XWV 195

SHIPPING DATA

Operating Weight 4192KG

Dimensions 3301mm L x 1264mm W x 2069mm H

MECHANICAL DATA

Water Connections	Victaulic/flanged
Flow Rate	27.56 L/S
Minimum Load	152 KW
Circuits / Compressors	1 / 1
Refrigerant / Charge	R134a

ELECTRICAL DATA

Voltage	415 V / 3 phase / 50 hertz
RLA	346 amps
Power Factor	0.91
FLA	195 amps

	Chiller Selection
Condenser Water – In/Out	30 °C/ 35 °C
Cooling Capacity	760 KW
Leaving Temperature	7 °C
Entering Temperature	12 °C