

設備名稱：可變冷媒流量多聯分離式空氣調節機 型號(型式)：MMY-MAP1204HT7-TW 及證書上所列之所有系列型號如附件

Equipment name：Split Type Air Conditioners Type designation(Type)：MMY-MAP1204HT7-TW 及證書上所列之所有系列型號如附件

單元 Unit	限用物質及其化學符號 Restricted substances and its chemical symbols					
	鉛 (Pb)	汞 (Hg)	鎘 (Cd)	六價鉻 (Cr <sup>+6</sup> )	多溴聯苯 (PBB)	多溴二苯醚 (PBDE)
室內機風扇馬達 Indoor unit fan motor	—	○	○	○	○	○
室外機風扇馬達 Outdoor unit fan motor	—	○	○	○	○	○
壓縮機 Compressor	○	○	○	○	○	○
控制電路板 Control PCB	—	○	○	○	○	○
熱交換器 Heat exchanger	○	○	○	○	○	○
外殼及其他金屬結構 Case & other metal components	○	○	○	○	○	○
銅管閥件 Piping, valves	—	○	○	○	○	○
配件 Accessories	—	○	○	○	○	○

備考1. “超出0.1 wt %”及“超出0.01 wt %”係指限用物質之百分比含量超出百分比含量基準值。

Note 1: “Exceeding 0.1 wt %” and “exceeding 0.01 wt %” indicate that the percentage content of the restricted substance exceeds the reference percentage value of presence condition.

備考2. “○”係指該項限用物質之百分比含量未超出百分比含量基準值。

Note 2: “○” indicates that the percentage content of the restricted substance does not exceed the percentage of reference value of presence. of presence condition.

備考3. “—”係指該項限用物質為排除項目。

Note 3: The “—” indicates that the restricted substance corresponds to the exemption.

系列型號一覽表：

MMU-AP0092H-TW	MMD-AP0074BH-TW	MMD-AP0481HFE-TW	MMK-AP0073H-TW	MMD-AP0184H-TW	MMC-AP0154H-TW
MMU-AP0122H-TW	MMD-AP0094BH-TW	MMD-AP0721HFE-TW	MMK-AP0093H-TW	MMD-AP0244H-TW	MMC-AP0184H-TW
MMU-AP0152H-TW	MMD-AP0124BH-TW	MMD-AP0961HFE-TW	MMK-AP0123H-TW	MMD-AP0274H-TW	MMC-AP0244H-TW
MMU-AP0182H-TW	MMD-AP0154BH-TW	MMD-AP0074SPH-TW	MMK-AP0153H-TW	MMD-AP0364H-TW	MMC-AP0274H-TW
MMU-AP0242H-TW	MMD-AP0184BH-TW	MMD-AP0094SPH-TW	MMK-AP0183H-TW	MMD-AP0484H-TW	MMC-AP0364H-TW
MMU-AP0272H-TW	MMD-AP0244BH-TW	MMD-AP0124SPH-TW	MMK-AP0243H-TW	MMD-AP0724H-TW	MMC-AP0484H-TW
MMU-AP0302H-TW	MMD-AP0274BH-TW	MMD-AP0154SPH-TW		MMD-AP0964H-TW	
MMU-AP0362H-TW	MMD-AP0304BH-TW	MMD-AP0184SPH-TW			
MMU-AP0482H-TW	MMD-AP0364BH-TW				
MMU-AP0562H-TW	MMD-AP0484BH-TW				