



Technical documentation-1/3

General description of the appliance
Multi-split

Outdoor side heat exchanger
air

Type of compressor driven
Vapor compression

Outdoor unit (1)
TypeName
XCT8 4HP
38V5121188JCEE

Indoor unit (1)
TypeName
Concealed Duct
40VD012S-8S-TEE

Indoor unit (3)
TypeName
Concealed Duct
40VD009S-8S-TEE

Indoor side heat exchanger
air

Driver of compressor
electric motor

Outdoor unit (2)
TypeName
-
-

Indoor unit (2)
TypeName
Concealed Duct
40VD009S-8S-TEE

Indoor unit (4)
TypeName
Concealed Duct
40VD009S-8S-TEE

Technical documentation-2/3

Function
cooling
heating
Y
Y

Item	symbol	value	unit
Design load			
Cooling	Pdesignc	12.1	kW
Heating	Pratedh	12.5	kW
heating/Average	Pdesignh	8.8	kW
heating/Warmer	Pdesignh	-	kW
heating/Colder	Pdesignh	-	kW

Declared capacity for cooling at indoor temperature 27(19)°C and outdoor temperature Tj.			
Tj=35°C	Pdc	12.10	kW
Tj=30°C	Pdc	9.03	kW
Tj=25°C	Pdc	5.89	kW
Tj=20°C	Pdc	5.67	kW
Degradation co-efficient	Cdc	0.25	

Declared capacity for heating/Average season, at indoor temperature 20 °C and outdoor temperature Tj			
Tj=-7°C	Pdh	7.75	kW
Tj=2°C	Pdh	4.72	kW
Tj=7°C	Pdh	3.86	kW
Tj=12°C	Pdh	4.26	kW
Tj=bivalent temperature	Pdh	7.75	kW
Tj=operation limit	Pdh	5.39	kW
Degradation co-efficient	Cdh	0.25	

Bivalent temperature			
heating/Average	Tbiv	-7	°C
heating/Warmer	Tbiv	-	°C
heating/Colder	Tbiv	-	°C

Electric power input in power modes other than active mode			
off mode	Poff	0.015	kW
standby mode	Psb	0.015	kW
thermostat-off mode	Pto	0.000	kW
crankcase heater mode	Pck	0.000	kW

Capacity control	
Fixed	N
Strage	N
Variable	Y

Average
Warmer
Colder
Y
N
N

Item	symbol	value	unit
Seasonal efficiency			
Cooling	η _{sc}	353.80	%
	SEER	8.92	-
heating/Average	η _{h(A)}	153.00	%
	SCOP(A)	3.90	-
heating/Warmer	η _{h(W)}	-	%
	SCOP(W)	-	-
heating/Colder	η _{h(C)}	-	%
	SCOP(C)	-	-

Declared Energy efficiency ratio for cooling at indoor temperature 27(19)°C and outdoor temperature Tj.			
Tj=35°C	EERd	4.03	-
Tj=30°C	EERd	6.44	-
Ti=25°C	EERd	10.99	-
Tj=20°C	EERd	17.43	-

Declared coefficient of performance/Average season, at indoor temperature 20°C and outdoor temperature Tj.			
Tj=-7°C	COPd	2.87	-
Tj=2°C	COPd	3.34	-
Tj=7°C	COPd	6.23	-
Tj=12°C	COPd	7.50	-
Tj=bivalent temperature	COPd	2.87	-
Tj=operation limit	COPd	2.36	-

Operation limit temperature			
heating/Average	Tol	-20	°C
heating/Warmer	Tol	-	°C
heating/Colder	Tol	-	°C

Supplementary heater		
elbu	-	kW

Refrigerant		
Type	R410A	
Weight	6.40	kg
Global warming potential GWP	2088	kgCO2eq

Technical documentation-3/3

Sound power level		
outdoor unit (cooling)	67	dB(A)
outdoor unit (heating)	67	dB(A)
outdoor unit (cooling)		dB(A)
outdoor unit (heating)		dB(A)
outdoor unit (cooling)		dB(A)
outdoor unit (heating)		dB(A)

Outdoor unit dimension	height	1235	mm
	width	990	mm
	depth	390	mm
weight		125	kg

Outdoor unit dimension	height		mm
	width		mm
	depth		mm
weight			kg

Rated air flow			
outdoor unit (cooling)	elbu	5660	m3/h
outdoor unit (heating)	elbu	5660	m3/h
outdoor unit (cooling)	elbu		m3/h
outdoor unit (heating)	elbu		m3/h
outdoor unit (cooling)	elbu		m3/h
outdoor unit (heating)	elbu		m3/h

Outdoor unit dimension	height		mm
	width		mm
	depth		mm
weight			kg

Harmonised standard	EN 14511-3:2013
---------------------	-----------------

Calculation methods	PrEN 14825:2016
Measurement standards	

Contact details for obtaining more information	Carrier HVAC Equipment(Hangzhou)Co.,Ltd No.181, Weiken Street, Baiyang Block, Hangzhou Qiantang Area, Zhejiang Province, China
--	---