



Model	38VT018188HTEE
Overall efficiency	46,4
Measurement category used to determine the energy efficiency A-D)	A
Efficiency category	static
Efficiency grade at optimum energy efficiency point	40
Whether the calculation of fan efficiency assumed use of a VSD and if so, whether the VSD is integrated within the fan or the VSD must be installed with the fan;	Integrated
Year of manufacture	2024
Manufacturer's name or trade mark, commercial number place of manufacture.	-
Product's model number	PF581-T
Rated motor power input(s) at optimum energy efficiency	0.423kW
Flow rate(s) at optimum energy efficiency	2.01m <sup>3</sup> /s
Pressure(s) at optimum energy efficiency	87.5Pa
Rotations per minute at optimum energy efficiency point	1050rpm
Specific ratio	1,0
Information relevant for facilitating disassembly, recycling or disposal at the end of life.	-
Information relevant to minimise impact on the environment and ensure optimal life expectancy as regards installation, use and maintenance of the fan.	-
Description of additional items used when determining the fan efficiency , such as ducts, that are not described in the measurement category and not supplied with the fan	-