

Lot11

№	Item	Model name	
		40VH150A-8S-CEE	40VH200A-8S-CEE
1	Overall efficiency(η)	35.5	38.8
2	Measurement category	A	A
3	Efficiency category	static	static
4	Efficiency grade at optimum energy efficiency point	First tier (2013/1) : 37 Second tier (2015/1) : 44	First tier (2013/1) : 37 Second tier (2015/1) : 44
5	VSD in integrated within the fan or the VSD must be installed with the fan.	The VSD is integrated within the fan.	The VSD is integrated within the fan.
6	Year of manufacture	2025	2025
7	Manufacture's name or trade mark ,commercial number and place of manufacture.	Carrier HVAC Equipment (Hangzhou) Co.,Ltd. China	Carrier HVAC Equipment (Hangzhou) Co.,Ltd. China
8	Product's model number	DHV4230012	DHV4230012
9	Rated motor power input(s)(kW)、flow rate(s) and pressure(s) at optimum energy efficiency	Power input 0.166 kW flow rate 0.157 m3/s pressure 323 Pa	Power input 0.272 kW flow rate 0.157 m3/s pressure 586 Pa
10	Rotations per minute at optimum energy efficiency point	1510 rpm	1900 rpm
11	Specific ratio	1.0	1.0
12	Information relevant for facilitating disassembly, recycling or disposal at the end of life.	-	-
13	Information relevant to minimise impact on the environment and ensure optimal life expectancy as regards installation, use and maintenance of the fan.	-	-
14	Description of additional items used when determining the fan efficiency , such as ducts, that are not described in the measurement category and not supplied with the fan.	-	-