



A legacy of innovation in air solutions
brings to you a range of air purifiers like no other.

Introducing,
AIR ONE

The surest way to
breathe pure





PM2.5 display Monitor air quality in real time

The purifier's smart PM2.5 display and colour indicator keeps you updated on the quality of air.



4 fan speeds Adjust the speed of purification as per your needs

With 4 fan speed options, you can now adjust the speed of filtration basis the indoor air quality.



Auto/silent mode A good night's rest is a touch of a button away

The silent mode dims the PM2.5 indicator's light and optimizes your purifier's performance to lower noise levels, so you can wake up fresher and more energized.



Filter replacement reminder Know when your purifier needs a change, easily


Never compromise on the quality of air you inhale with the handy filter replacement reminder.





UltraSafe Technology

To kill 99.99%* Viruses and Bacteria



Active Carbon filter + Photo Catalyst (2 in 1)

Active Carbon: Removes VOCs & unpleasant odor.
Photo Catalyst filter: Ultraviolet light irradiates titanium dioxide nanoparticles, to produce hydroxyl ions (-OH), which are highly oxidizing and can damage cell walls, rendering bacteria and virus instantly inactive.

Pre Filter

A fine mesh filter to block large particles like pet fur, dander & dust.

UV Light

A cold cathode UV Lamp can effectively kill and inhibit the growth of viruses and bacteria.

HEPA Filter

A high-efficiency filter to block particles of size upto 0.3 microns.

*UV + Photocatalyst Test Result: H1N1 Virus Elimination Rate : ≥ 99.99%
Guangzhou Institute of Microbiology, China

AP2006



AP3006



AP6006



| Model Name | CADR (m ³ /hr) | Area Covered (sq. ft.) | Product Dimensions HxWxD (cm) | Weight (kg) | Power Consumption (Watt) |
|------------|---------------------------|------------------------|-------------------------------|-------------|--------------------------|
| AP2006 | 260 | 300 | 53.5x34.7x17.5 | 5.2 | 20 |
| AP2006 UV | 260 | 300 | 53.5x34.7x17.5 | 5.2 | 23 |
| AP3006 UV | 360 | 550 | 62.8x41.0x21.0 | 7 | 33 |
| AP6006 UV | 510 | 760 | 71.0x46.0x23.0 | 10 | 66 |

Note: Area Calculated at 3 ACH.

Why do you need an air purifier?

On an average, we spend more than 75% of our time indoors. However, indoor air is often more polluted than the air outside:

1. Indoor smoke contains a range of health-damaging pollutants, such as small particles and carbon monoxide. In fact, particulate pollution levels may be 20 times higher than accepted guideline values.
2. Household air pollution causes several diseases, including pollen allergies, stroke, heart diseases, Chronic Obstructive Pulmonary Disease (COPD), and even lung cancer.

An air purifier helps you by eliminating harmful pollutants, and purifying the indoor air.

How to choose the right air purifier?

Choosing the right air purifier for your room depends on two factors:

1. Clean Air Delivery Rate (CADR): The rate at which an air purifier delivers clean air, usually measured in CMH (Cubic Metre/Hour). This value is defined by the manufacturer.
2. Air Changes per Hour (ACH): The number of times the air inside a room passes through an air purifier, within an hour. For example, if the air inside your room is purified every 20 minutes, your air purifier undertakes 3 air changes in an hour.

You can calculate the area covered by the air purifier using the formula: $CADR / (1.7 \times 8 \times ACH)^*$

*1.7 is the standard conversion of CMH (Cubic Metre/Hour) to CFM (Cubic Feet/Min). 8 is the standard height of the room in feet.

What does each filter do?

1. Pre-filter: Filters larger dust particles, hair and dead skin.
2. UV and Photocatalyst: Ultraviolet light irradiates titanium dioxide nanoparticles, to produce hydroxyl ions (-OH), which are highly oxidizing and can damage cell walls, rendering bacteria and virus instantly inactive.
3. HEPA filter: Removes smaller particles of size PM0.3–2.5, pollens and allergens.
4. Activated Carbon filter: Keeps the room smelling fresh by eliminating pet odour, smoke, paint smell and VOCs.



CARRIER SERVICE HELPLINE
1800 3000 3545
1800 1021 421

For more details, please contact our sales office:

Corporate & Registered Office: Carrier Airconditioning & Refrigeration Ltd, Kherki Daula Post, Narsingpur, Gurgaon 122004, Tel: 0124-4825500
Sales Offices: – Ahmedabad: 079-44820400 Ghaziabad: 0120-4183260 Bangalore: 080-43442000 Bhubaneswar: 9778030033 Chandigarh: 0172-5007549/50 Chennai: 044-66448888 Cochin: 0484-4029001 Coimbatore: 7397444250 Delhi/NCR: 0124-4873200 Hyderabad: 040-41812233 Indore: 9810204975 Jaipur: 0141-4921737 Kolkata: 033-4059-2000/3000 Lucknow: 0522-4158701 Mumbai: 022-61700700 Pune: 020-48571000/01
 CIN: U74999HR1992FLC036104/ Website: www.carrierindia.com/ E-mail: customersupport@carrier.com

