

THE DIFFERENCE IS IN THE DETAIL

GENERAL	4	
STANDARDS	6	
2.1 Mechanical strength	6	
2.2 Casing air leakage	7	
2.3 Filter bypass leakage	7	
2.4 Thermal transmission	8	
2.5 Thermal bridges	8	
2.6 Acoustic casing insulation	9	
SIZING	10	
CASING	10	
4.1 Frame	11	
4.1.1 Casing profile	11	
4.1.2 Plastic corners	12	
4.1.3 Connection posts	12	
4.2 Casing wall	13	
4.2.1 Panels	13	
4.2.2 Centre posts	14	
4.2.3 Doors and inspection hatches	14	
INLET/MIXING SECTION	17	
5.1 Flexible connections	18	
5.2 Dampers	19	
FILTERS	20	
6.1 Slide-infilters	21	
6.2 Built-in filters	22	
6.3 Absolute Filters	22	
6.4 Delta sections	23	
6.5 Carbon filters	23	
SPECIAL INLET SECTION	24	
FROST PROTECTION COIL	25	
HEAT RECOVERY	26	
	27	
	28	
9.3 Run-around coil systems	28	
HEATING COILS	29	
10.1 Hot water	29	
10.1.1 Frost protection thermostat	30	
	STANDARDS 2.1 Mechanical strength 2.2 Casing air leakage 2.3 Filter bypass leakage 2.4 Thermal transmission 2.5 Thermal bridges 2.6 Acoustic casing insulation  SIZING  CASING 4.1 Frame 4.1.1 Casing profile 4.1.2 Plastic corners 4.1.3 Connection posts 4.2 Casing wall 4.2.1 Panels 4.2.2 Centre posts 4.2.3 Doors and inspection hatches  INLET/MIXING SECTION 5.1 Flexible connections 5.2 Dampers  FILTERS 6.1 Slide-infilters 6.2 Built-in filters 6.3 Absolute Filters 6.4 Delta sections 6.5 Carbon filters  SPECIAL INLET SECTION  FROST PROTECTION COIL  HEAT RECOVERY 9.1 Heat recovery wheels 9.2 Plate heat exchangers 9.3 Run-around coil systems  HEATING COILS	STANDARDS       6         2.1 Mechanical strength       6         2.2 Casing air leakage       7         2.3 Filter bypass leakage       7         2.4 Thermal transmission       8         2.5 Thermal bridges       8         2.6 Acoustic casing insulation       9         SIZING       10         CASING       10         4.1 Frame       11         4.1.1 Casing profile       11         4.1.2 Plastic corners       12         4.1.3 Connection posts       12         4.2 Casing wall       13         4.2.1 Panels       13         4.2.2 Centre posts       14         4.2.3 Doors and inspection hatches       14         INLET/MIXING SECTION       17         5.1 Flexible connections       18         5.2 Dampers       19         FILTERS       20         6.1 Slide-infilters       21         6.2 Built-in filters       22         6.3 Absolute Filters       22         6.4 Delta sections       23         6.5 Carbon filters       23         SPECIAL INLET SECTION         24         FILTERS PROTECTION COIL         <



11) COOLING COILS	31	
11.1 Chilled water	32	
11.2 Direct expansion (E	DX) 32	
12) HUMIDIFIERS	33	
12.1 Steam humidificati		
12.2 Water spray banks		
12.2.1 Infrasonic	35	
12.2.2 Ultrasonic	35	
12.2.3 Water/pres	surised air 36	
12.2.4 Hybrid	36	
12.3 Conventional	36	
12.3.1 Spray humi	idifier 36	
12.3.2 Wet-cell hu		
13) FANS	37	
13.1 Centrifugal fans	38	
13.2 Motors	38	
	39	
13.3 Transmission		
13.4 Mounting	39	
13.5 Options	40	
13.6 Direct-drive centrife		
13.7 Plug fans	41	
13.8 Other fans	41	
14) SOUND ATTENU	ATORS 41	
15) DISCHARGE	42	
16) OUTSIDE INSTAL	LATION 43	
17) ACCESSORIES	45	
18) CONTROL	48	
19) INSTALLATIONS	49	
19.1 Health Care	49	
19.2 Shopping Centers	50	
19.3 Tourist Centers	51	
19.4 Schools and Univer	rsities 52	
19.5 Industrial Facilities	53	
19.6 Offices, Banks and	Government 53	
19.7 Cultural Centers, R	decreation and Theatres 54	
19.8 Airports	54	
19 9 Other	55	



#### General

When you choose Carrier products your choice is backed by over 50 years experience in the field of air handling. For your day-to-day work this means that you will receive a balanced high-quality modular air handling system. A system that can also be easily integrated with other Carrier systems, such as chilled-water units, fan coil units and roof fans. This means that you always have the assurance of an optimised heating, ventilation and air conditioning (HVAC) installation in your building.

As a user you have every right to demand high-efficiency air handling systems. Certification of our processes according to the international quality standard ISO 9001:2000 is your guarantee for the quality of the Carrier product offering and the services provided. For complete peace-of-mind a large number of Carrier products are also Eurovent-certified, giving the customer the assurance that the published product performances are correct. Of course Carrier also complies with all Environment, Health & Safety (EH&S) regulations and takes a resonsible and caring approach to environment, health and safety matters. We are fully committed to safeguarding our environment for future generations.

#### **Carrier and the environment**

At Carrier we care for 'everything that lives', and this is emphasised by the use of the most ozone-friendly refrigerants in our units and systems. More and more of our machine components are recyclable, and Carrier is also one of the pioneers in the use of energy-saving technologies and production processes. In short, our systems already meet tomorrow's standards today.



#### Carrier in short

United Technologies Corporation is a well-known American corporation that is quoted on the stock exchange. Carrier Corporation is just one of the subsidiaries of this large world-wide organisation. In the Netherlands Carrier Corporation is represented by various Carrier companies that are active in the fields of heating, ventilation, air conditioning, as well as transport and commercial refrigeration. Carrier Holland Heating is the world-wide Carrier expert for air handling units. Carrier Holland Heating and Alarko Carrier are the only manufacturing points of 39 HQ air handling units for EMEA market.





#### **Research & Development**

To maintain the top position in the area of air treatment in the world, product research and development continues to be one of Carrier's top priorities. Besides its 45 production centres spread all over the world Carrier also has 14 R & D units with a total annual budget of over 400 million Dollars. These carry out continuous research in important sectors such as acoustics, compressor technology, new refrigerants and metallurgy.



In the European R & D centres in Montluel,
France and Waalwijk in the Netherlands we conduct pioneering research projects that result in important product innovations.
Carrier's innovative approach is underlined by the number of patents we have

recently received, including patents in the air treatment area.



# Spotlight on Carrier Holland Heating and Alarko Carrier

Inside the world-wide Carrier organisation Carrier Holland Heating in Waalwijk is the knowledge centre for air handlings units. Here we develop innovative software programs for the selection and evaluation of components for air handling units - from vibration mounts to fan belt drives and to operating cost calculations for heat recovery systems and start-up times for fan/motor combinations. But the Carrier Holland Heating expertise is also welcomed outside Carrier.



The company also participates on platforms with the objective of developing and maintaining international and European standards in the field of air handling (EN1886 and EN13053). It also actively participates in compiling various Eurovent publications on air handling units. The Dutch branch of Carrier is now represented in the European Certification Programme for Air Handling Units that covers initiatives to improve the quality and integrity of the certification procedure.

Alarko Carrier is the second manufacturing factory of Air Handling Units for Carrier and with his great knowledge and experience, serves market most reliably units.



#### 2 STANDARDS

There are two European standards on air handling units that describe the characteristics of the casing wall construction and the classification and performances of units, components and sections, respectively:

EN 1886 - 1998
 "Air handling units – Mechanical performance"

• EN 13053 - 2001

Air handling units – Ratings and performance for units, components and sections

Both standards have been revised and now also exist as a prEN standard.

The characteristics of the casing wall construction must be established in accordance with EN 1886, based on measurements carried out on a model box and a real unit.

A model box is an air handling unit without its installed components that consists of two sections with a joint. Each section also has a door. The dimensions and the construction must comply with the requirements of the standard.

Thermal and acoustic characteristics of a casing wall construction are exclusively determined on the basis of measurements taken on the model box, while mechani-cal strength, air leakage and filter bypass leakage must be determined on the basis of measurements taken on a real unit, that has been designed for an HVAC application. The classes for the last three characteristics may also be determined for a model box, if this is clearly indicated.

### 2.1 Mechanical strength

There are two test criteria for mechanical strength:

- relative deflection [mm x m<sup>-1</sup>] of posts and panels under normal design conditions
- $\bullet$  mechanical resistance [no permanent deformation] against maximal fan pressure

When testing the mechanical strength of the model box, the following test pressures apply:

Deflection

- 1500 Pa over and under-pressure in accordance with EN 1886 1998
- 1000 Pa over and under-pressure in accordance with prEN 1886

Fan pressure

- 2500 Pa over and under-pressure in accordance with EN 1886 1998
- 2500 Pa over and under-pressure in accordance with prEN 1886

The standard differentiates between the following classes:

Mechanical classes in accordance with EN 1886 - 1998    Deflection class								
Deflection class  Maximum relative deflection mm x m <sup>-1</sup> 1 10  1B No requirements 1A 10	ı							
Deflection class	eflection class deflection maximum fan							
1	10	No	-					
1B	No requirements	Yes						
1A	10	Yes						
2	4	No	*					
2A	4	Yes	+					

Mechanical classes i	n accordance with pr	EN 1886	
Deflection class	Maximum relative deflection mm x m <sup>-1</sup>	Resistance against maximum fan pressure	Quality
D1	4	Yes	+
D2	10	Yes	<b>†</b>
D3	No requirements	Yes	-

In the tables the classes the standard construction model box GP080\* complies with are marked in blue.

<sup>\*</sup>see chapter 4 "Casing"



## 2.2 Casing air leakage

Depending on the construction of the air handling unit and the nominal operating pressures air leakage is measured at the following test conditions:

- all sections at 400 Pa negative pressure, if there is only negative pressure in the unit
- positive pressure sections at 700 Pa or higher positive pressure, if the operating pressure after the fan is higher than 250 Pa. If the operating pressure that

occcurs is higher than 700 Pa, the positive pressure sections are tested under actual pressure conditions. The remaining sections are tested at 400 Pa negative pressure.

The permissible air leakage is linked to the filter class in the relevant casing section. The tables below list the air leakage classes together with the associated filter classes.

Air leakage classes in accordance with EN 1886 - 1998  Leakage class  Maximum leakage at - 400 Pa l x s <sup>-1</sup> x m <sup>-2</sup> Al 3.96  Maximum leakage at + 700 Pa l x s <sup>-1</sup> x m <sup>-2</sup> Acc. to EN 779  G1-G4  G1-G4									
Leakage class	at - 400 Pa	at + 700 Pa	filter class	Quality					
3A	3.96	5.70	G1-G4	-					
А	1.32	1.90	F5-F7						
В	0.44	0.63	F8-F9	+					

Air leakage cla	sses in accordance	e with prEN 1886		
Leakage class	Maximum leakage at- 400 Pa l x s <sup>-1</sup> X m <sup>-2</sup>	Maximum leakage at + 700 Pa l x s <sup>-1</sup> x m <sup>-2</sup>	Maximum filter class acc. to EN 779	Quality
L1	0.15	0.22	Better than F9	+
L2	0.44	0.63	F8-F9	<b>^</b>
L3	1.32	1.90	G1-F7	· -

In the tables the classes the standard construction model box GP080\* complies with are marked in blue.

## 2.3 Filter bypass leakage

Filter bypass leakage refers to the total amount of unfiltered air after the filter section.

The unfiltered air flow is the sum of:

- air that passes the filter medium outside the filter section
- air leakage through the walls of the sections after the filter, with negative pressure

Bypass leakage through the filter section is measured at a pressure difference of 400 Pa over the filter section, and filters are sometimes replaced by dummy plates with an air tightness mechanism identical to the one of the filters.

The tables below list the total admissible bypass leakage k in % of the design air flow over the filters as a function of the built-in filter class.

Maximum admissible filter	r bypass lea	akage in acc	ordance wit	h EN 1886 –	1998	
Built-in filter class	G1- G4	F5	F6	F7	F8	F9
Total bypass leakage k %	-	6	4	2	1	0.5

Maximum admissible filter	bypass leakag	e in accordance	with prEN 188	36	
Built-in filter class	G1- F5	F6	F7	F8	F9
Total bypass leakage k %	6	4	2	1	0.5

The standard slide-in construction for filters, tested in a model box, is suitable for filter class F9; if marked in blue in the tables. In accordance with standard prEN 1886 this is based on a face velocity of 2.5 m/s over the filter (e.g. 0.93 m³/s for a 610 x 610 mm filter).

<sup>\*</sup> see chapter 4 "Casing"



#### 2.4 Thermal transmission

The thermal transmission of a model box is the average heat transfer coefficient of the construction in W x m $^{-2}$  x K $^{-1}$ , referred to the external surface.

The measurement is carried out with heat sources in the model box, where the total power input and the average temperature difference between inside and outside is determined at a stable condition. Thermal transmission is the ratio between the total power input and the internal/external surface temperatures times their surface area. Depending on the measured values the construction has in one of the following classes:

Thermal transmission U a	according to EN 1886 - 1998	& prEN 1886
CLASS	HEAT TRANSFER COEFFICIENT [Wxm <sup>-2</sup> xK <sup>-1</sup> ]	QUALITY
T1	U ≤ 0.5	+
T2	0.5 < <i>U</i> ≤ 1.0	<b>A</b>
T3	1.0 < <i>U</i> ≤ 1.4	
T4	1.4 < <i>U</i> ≤ 2.0	
T5	No requirements	-

The standard construction GP080\* complies with class T2, and it is marked in blue in the table.

### 2.5 Thermal bridges

The thermal bridging factor of a model box is measured for the same set-up that is used to determine the heat transfer coefficient.

At the stable condition the highest detectable surface temperature on the outside surface of the model box is measured.

The thermal bridging factor is the quotient of indoor air temperature minus highest surface temperature and the air temperature difference between inside and outside. The measured value is in one of the classes below and indicates if there is surface condensation or not. As the thermal bridging factor increases, the possibility of condensation decreases.

For classes TB3 and TB4 1% of the external surface may have a higher temperature than the maximum admissible value for the class in question; this does not apply for classes TB1 and TB2.

Thermal bridging factor	k₅ according to EN 1886 - '	1998 & prEN 1886	
CLASS	Thermal bridgi	ng factor [kʰ]	QUALITY
CLASS	EN 1886 - 1998	prEN 1886	QUALITY
TB1	0.75 < k <sub>b</sub> ≤ 1.0	0.75 ≤ k <sup>b</sup> < 1.0	+
TB2	0.60 < k <sub>b</sub> ≤ 0.75	0.60 ≤ k♭ < 0.75	<b>A</b>
TB3	0.45 < k <sub>b</sub> ≤ 0.60	0.45 ≤ k <sup>b</sup> < 0.60	
TB4	0.30 < k <sub>b</sub> ≤ 0.45	0.30 ≤ k <sup>b</sup> < 0.45	
TB5	No requirements	No requirements	-

The standard construction GP080\* complies with class TB2, and it is marked in blue in the table.

<sup>\*</sup> see chapter 4 "Casing"

<sup>\*</sup> see chapter 4 "Casing"



# 2.6 Acoustic casing insulation

Acoustic casing insulation, as defined by EN 1886, is the attenuation achieved by enclosing a noise source with a model box.

For this purpose the average sound pressure level of a noise source placed on the floor, is measured in an imaginary enclosing area. The measurement is repeated in the same enclosing area, but with the noise source in the model box. The difference in the measured sound pressure levels, divided into octave bands of 125 to 8000 Hz, is the attenuation of the casing wall construction, including the doors and joint. For the standard casing wall construction GP080 the measured attenuation is shown in the table below.

Acoustic casing insulation in accordance with EN 1886-1998 & prEN 1886         Average octave band frequency [Hz]       125       250       500       1000       2000       4000       8000         Attenuation [dB]       18.9       19.1       20.4       21.8       21.2       30.4       36.3									
Average octave band frequency [Hz]	125	250	500	1000	2000	4000	8000		
Attenuation [dB]	18.9	19.1	20.4	21.8	21.2	30.4	36.3		

Note: As detailed above this is for a complete AHU construction, not just a panel in the wall type test.



#### 3 SIZING/RANGE

- 122 different standard sizes
- nominal selection range between 0.55 m³/s (2000 m³/h) and 35 m³/s (125.000 m³/h)
- sizes in the preferred range with increasing air flows in steps of approx. 12%
- optimised selection possible for each air flow and each configuration
- installation types for indoor, outdoor, vertical and ceiling mounting and stacked.
- flexibility
- made-to-measure

Width Module height	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	
2,5	0.56	0.69	0.38																				]
4	1.11	1.39	1.67	1.81	2.22	2.50	2.78	3.06	3.33														
6	1.67	2.22	2.50	2,92	3.33	3.75	4.17	4.72	5.00	5.56	5.83	6.39	16.67	7.22	7.50								1
8			3.33	3.89	4.44	5.00	5.56	6.11	6.57	7.22	7.78	8.33	8.89	9.44	10.00	10.56	11.11	11.67	12.22	12.78	13.33		1
10					5.56	6.39	6.94	7.64	8.33	9.03	9.72	10.56	11.11	11.94	12.50	13.33	13.89	14.72	15.28	16.11	16.67	17.50	1
12						7.50	8.33	9.17	10.00	10.83	11.67	12.50	13.33	14.44	15.00	15.83	16.67	17.50	18.33	19.17	20.00	20.83	1
14									11.67	12.78	13.61	14.72	15.56	16.67	17.50	18.61	19.44	20.56	21.39	22.50	23.33	24.44	1
16										14.44	15.56	16.67	17.78	18.89	20.00	21.11	22.22	23.33	24.44	25.56	26.67	27.78	1
18															22.50	23.89	25.00	26.39	27.50	28.89	30.00	31.39	Ī
20																	27.78	29.17	30.56	31.94	33.33	34.72	,

Preferred range

Combination with heat recovery

Other sizes

\* values are in m³/s

\*\* larger sizes are possible upon request

Module dimension: 160 mm External width: n x module plus 100 mm External height: n x module plus 100 mm Base frame height: 160 mm or 62 mm Example: type 39HQ12.10 Width: 12 x 160 plus 100 = 2020 mm

Height:  $10 \times 160$  plus 100 = 1700 mm excl.base frame

Nominal air flow: 8.33 m³/s

#### 4 CASING

The construction of the Carrier air handling units consists of a frame and panels. Profiled 1-mm thick casing sides of galvanised and coated steel plates ensure a rigid and lightweight frame. The frame holds a 60-mm dual-skin casing wall with panels, doors, inspection hatches and removable centre posts. The casing wall construction comes in several versions of steel plate thicknesses, material types and insulation materials used.

The internal plating is always 0.8 mm thick. The standard casing wall construction GP080 consists of 0.8 mm internal and external plating with mineral wool (glass wool) in between. The floor panel of the standard casing

wall construction is made with PIR (polyisocyanurate) insulation for enhanced thermal characteristics and the possibility to walk on it. Compared with PUR, PIR insulation has an increased insulation value and improved fire resistance. Other advantages of PIR insulation are high pressure resistance and the possibility to walk on it. As various markets have different requirements there are also versions with rock wool insulation and other panel thicknesses and plate materials, such as stainless steel.

The RR125 acoustic version has an additional acoustic plate in the internal shell especially designed to efficiently dampen low-frequency sounds.

#### GP080

G = insulation, side and roof panels

P = insulation, floor panel

080 = thickness of the external plating

(G = glass wool, R = mineral wool)

(P = PIR, R = mineral wool) (080 = 0.80 mm / 125 = 1.25 mm)

10

4

4



Panel	Thermal transmission fact	Thermal bridging tor	Air leakage	Acoustic casing insulation (dB)							
type					125 Hz	250 Hz	500 Hz	1 kHz	2 kHz	4 kHz	8 kHz
GP080	T2	TB2	B (L2)	Attenuation (dB)	19	19	20	22	21	30	36
RP080	T2	TB2	B (L2)	Attenuation (dB)	17	20	20	22	21	29	36
RR125 (acoustic)	ТЗ	TB3	B (L2)	Attenuation (dB)	26	27	27	25	25	31	36

- aesthetic styling
- no deformation during transport, installation and operating life due to stable post construction
- panels removable by using centre posts
- air handling unit surfaces smooth inside and outside without protruding parts

- durable
- can be assembled on site
- maintenance and userfriendly



#### 4.1 Frame

#### 4.1.1 Casing profile

- no air circulation in profiles, profiles fully welded and hermetically sealed at the ends
- 1 mm thick steel plate (galvanised and coated) with metal anchors means that screws go into a thicker material and the construction is more robust, airtight and can be repeatedly disassembled
- resistant against over- and under-pressure up to 2500 Pa
- optimal energy efficiency
- durable
- corrosion resistant
- hygienic



Casing profile



Metal anchors



#### 4.1.2 Plastic corners

- corner hermetically sealed by airtight bulkheads
- shock-proof and stable ABS
- resistant against weather aggression and high and low temperatures
- corrosion resistant
- durable
- hygienic




ABS plastic corner



Airtight bulkheads

#### **4.1.3 Connection posts**

- not longer than module size, using unique coupling system
- air handling unit stays flat due to the use of a coupling strip
- connections flat on both sides; air tightness and thermal performances guaranteed after connection
- space-saving
- made-to-measure
- maintenance-friendly
- hygienic
- optimal energy efficiency



Connection post



Connection strip




# 4.2 Casing wall

#### **4.2.1 Panels**

- made of durable galvanised sheet steel treated with a weather and scratch-resistant coating on both sides
- closed interior using sealing flanges and sealing joints
- panels are airtight, vapour-resistant and corrosion-resistant
- floor panels filled with PIR, can be walked on
- panels frequently removable by using quality materials
- non-flammable glass or rock wool insulation material
- base colour light grey (RAL 7035)

- optimal energy efficiency
- durable
- maintenance and user-friendly
- corrosion-resistant
- safe
- noise dampening





60 mm thick panel



Closed interior

Panel coating





Easy to remove Floor panel with PIR


13




#### 4.2.2 Centre posts

- easily removable
- air handling unit has easy access, making components easy to reach and replace
- minimal bypass over the part by sealing
- airtight sealing by special covers

- maintenance and userfriendly
- optimal energy efficiency
- durable
- hygienic





Centre post with plastic cover

Plastic cover

#### 4.2.3 Doors and inspection hatches

- completely smooth inside surface
- doors and inspection hatches have the same thickness (60 mm) as the panel. The technical specification of the casing wall remains the same when a door or hatch is included
- no thresholds
- wear-resistant plastic roller bearing prevents damage to the casing wall
- hinge
  - stable construction makes adjustment unneccessary
  - durable through use of plastic bearing bushings
  - fully fixed
- airtight and vapour-resistant
- airtight seal using rubber sealing strip
- easy access with variable dimensions up to 3 metres high
- minimum of two locking points one with a lock that can only be opened with a special key
- high locks can be connected at the bottom
- several types of handles:
  - L grip
  - L grip 4-sided lock
  - L grip cylinder lock
  - inside hand grip
  - overpressure safety device

- durable
- optimal energy efficiency
- maintenance and user-friendly
- hygienic
- safe



Door post




Roller bearing



Hinge



No threshold



Fully fixed





Lock





Special key



Door







Overpressure safety device







Handle with 4-sided lock

inside hand grip

# 5 INLET/MIXING SECTION



INLET/MIXING SECTION







## **5 INLET/MIXING SECTION**

- inlet openings possible in all positions:
  - full face
  - half face (top, middle, bottom)
  - roof and floor
  - service- and non-service side
- shorter length for middle inlet opening for optimal air distribution

• made-to-measure







Full face Top connection Middle connection

#### 5.1 Flexible connections

- standard single-skin
- option: acoustic and thermal
- material used is environmental friendly and fire-safe Bisonyl
- completely airtight seal on aluminium connection profile
- high-quality finish
- quality
- safe








Detail flexible fan connection




# **5.2 Dampers**

- minmium air resistance due to airofoil shape
- airtight seal due to rubber seals on both damper blades and frame
- double maintenance-free bearing, optional special plastic version for humid spaces
- optionally finished with a 2-layer epoxy coating
- standard with opposed rotation
- in-built dampers to reduce leakage
- damper blade shaft airtight due to casing wall
- dampers with synchronised rotation for linear control characteristic of mixing sections
- optimised free passage due to damper blades with variable distance
- minimal air resistance
- made-to-measure
- durable
- hygienic



Variable distance



Mixing section




Airofoil damper with rubber seals



Opposed rotation



Synchronised rotation



Through damper shaft



Linkage construction



Actuator



Rubber seals in frame



# 6 FILTERS



20



#### **6 FILTERS**

All possible filter types such as pre-filters, panel, bag, pleated, electrostatic, chemical, carbon, hepa, ulpa and sand filters are available.

#### 6.1 Slide-in filters

- bag filters can easily be removed from the outside in one move, by using filter frame coupling brackets
- shorter casing length required
- slide-in filters possible for all sizes
- minimal bypass leakage up to and including filter class F9
- filter pressed against the filter frame by the filter positioning bracket
- filter profiles and fixing material standart galvanized steel, optional 304L or 316L stainless steel
- use of differential pressure gauge indicates when filters require changing
- space-saving
- maintenance-friendly
- hygienic
- optimal filter efficiency
- long life



Filter row can be completely pulled out in one move



Stainless steel 316L filter profile



Differential pressure gauge



Combination filter



Filter positioning bracket



### 6.2 Built-in filters

- user-friendly, self-locking filter holding bracket
- holding bracket stays in the filter module space during filter change
- minimal bypass leakage up to and including filter class F9
- filter profiles and fixing material made of galvanized steel, 304L or 316L stainless steel
- maintenance and user-friendly
- optimal filter efficiency
- hygienic
- durable





Filter holding bracket



User-friendly

### **6.3 Absolute filters**

- framework fully welded and coated
- simple positioning using innovative support construction
- held in place using a support bar construction

- maintenance and user-friendly
- durable



Welded framework



Support construction



Support construction



Support bar construction



# 6.4 Delta sections

- advanced filter technology for archives, libraries and museums specially developed by Carrier
- Delta sections:
  - electrostatic filter
  - chemical filter
  - carbon filter
  - particle filter

- innovative
- optimal conditioned air
- durable






Delta section Delta section

## 6.5 Carbon filters

• absorbs smells from the passing air stream

• hygienic



Carbon filter

# 7 SPECIAL INLET SECTION





### **7 SPECIAL INLET SECTION**

- robust 316L stainless steel drain pan, pre- and sub-filter with drain and siphon
- droplet eliminator integrated in the drain pan
- filter profiles in 304L or 316L stainless steel and corrosion-resistant fixing materials
- side wall in corrosion-resistant version
- walls and doors with drip panels
- safety and quality using robust protection profile
- fewer moisture droplets in the air as a result of low air velocity using the full face
- long life
- corrosion resistant
- maintenance and user-friendly
- safe







Door with drip panel



Entering threshold

#### **8 FROST PROTECTION COIL**

- heating coils before the filter reduce the relative humidity
- no humidity in the filters

- corrosion-resistant
- long life



Frost protection coil



# 9 HEAT RECOVERY





# 9.1 Heat recovery wheels

- 1) Condensation rotor
- 2) Hygroscopic rotor
- 3) Sorption rotor
  - efficient energy recovery method
  - total energy savings of heat recovery wheel systems can be determined with the operating cost calculation program developed by Carrier
  - standard version with access hatch
  - bearings accessible for maintenance
  - heat recovery wheel casing connects to air handling unit casing
  - various installation possibilities: sloped installation, installation with or without inspection hatch and added sections
  - housing corrosion-resistant
  - permanent seal using adaptive perimeter seal

- optimal energy efficiency
- low operating costs
- maintenance and user-friendly
- hygienic




Access hatches/inspection section



Heat recovery wheel





Screen shot of the operating cost calculation program







Seal

27

Drive



# 9.2 Plate heat exchangers

- Insulated drain pan with drain and siphon
- droplet elminator, depending on the model
- optimal use of the air handling unit cross section
- complete separation of supply and return air
- bulkhead insulated
- optionally equipped with face and bypass dampers
- optionally equipped with integrated recirculation dampers
- total energy savings of heat recovery wheel systems can be determined with the operating cost calculation program developed by Carrier
- optimal energy efficiency
- fully controllable



Drain pan with drain



Plate heat exchanger





Face and bypass damper

## 9.3 Run-around coil systems

- air handling units with separate supply and return air possible
- completely separate air flows

- flexible
- hygienic







#### **10 HEATING COILS**

#### 10.1 Hot water

- optimised coil fin surface as a function of the header diameter
- equipped with wire connections as standard
- Victaulic/Gruvlock flanges available
- heat exchanger in Cu/Al, pre-painted Cu/Al, Cu/Cu, FeZn, stainless steel
- casing Sendzimir or stainless steel
- coils selected based on environmental and economical reasons, water-side pressure drop for low primary energy costs in accordance with the Eurovent recommendations for calculation of energy consumption for air handling units
- optimal energy efficiency
- durable



Heating coil



Steam heating coil





Threaded connection





#### **10.1.1 Frost protection thermostat**

- special arrangement developed by Carrier
- each circuit has individual freeze-up protection
- ideal in combination with low-temperature systems
- reliable operation at low leaving air temperatures

- safe
- high-quality
- reliable



Arrangement of the frost protection thermostat

#### 10.2 Electric heaters

- terminal box fully integrated in the air handling unit
- possibility of placing gland connections at the top or bottom
- terminal box includes a connection diagram
- capacity step element evenly distributed over the casing section
- protection and maximum thermostat

- made-to-measure
- optimal energy efficiency



Even distribution



Rollers Terminal box



# 11 COOLING COILS





#### 11 COOLING COILS

#### 11.1 Chilled water

- optimised coil fin surface as a function of the header diameter
- coils selected based on environmental and economical reasons, water-side pressure drop for low primary energy costs in accordance with the Eurovent recommendations for

calculation of energy consumption for air handling units

- droplet eliminator behind the cooling coil easily removable at the air leaving side, making the coil and drain tray easy to clean
- stainless steel drain pan sloped towards the drain on the service side
- patented underpressure siphon

- optimal energy efficiency
- low operating costs
- hygienic
- maintenance and user-friendly









Easy to clean

### 11.2 Direct expansion (DX)

- connections easily accessible
- access for connections and maintenance using an expandable hatch of the same material as the casing
- droplet eliminator after the cooling coil easily removable on the air leaving side, making the coil and drain tray easy to clean
- maintenance-friendly
- flexible









Compressors

# 12 HUMIDIFIERS





#### 12 HUMIDIFIERS

#### 12.1 Steam humidification

Applicable for operating steam (life steam). If there is no operating steam, local steam humidifiers are available in gas-fired and electrical versions

- unique steam humidification section developed and patented by Carrier
- pre-installed steam humidifier available from various manufacturers
- all components are resistant to humidity
- humidifier equipped with waterproof lighting
- access door equipped with a window
- controlled condensate removal using a condensate drain valve developed by Carrier
- steam distribution available with multi-pipe systems (shorter inlet route)

- innovative
- space-saving
- hygienic
- maintenance and user-friendly



Section with distribution pipes



Steam venturi and vortex plate




## 12.2 Water spray banks

Atomisers are available in four versions: infrasonic, ultrasonic, water/pressurised air and hybrid.

#### 12.2.1 Infrasonic

- works with demineralised (RO) water
- humidification possible up to the saturation zone by adiabatic cooling
- unlimited control range
- excellent proportional control
- low energy usage
- durable components
- easy to install and maintain
- ideal for renovation projects
- includes pump unit and control
- short length
- guaranteed inlet length

- innovative
- optimal energy efficiency
- hygienic
- durable
- maintenance and userfriendly
- high quality



Horizontal cross section of infrasonic humidifierer

- 1. Infrasonic generator
- 2. Atomiser
- 3. Distribution box
- 4. Secondary generator
- 5. Inspection door
- 6. Saturated steam drier
- 7. Water removal8. Water collector
- 9. Intake route



Atomiser



Intake route

#### 12.2.2 Ultrasonic

- hygienic and legionella-proof
- proportional control possible
- equipped with an automatic hygienic dehumidification and rinse system
- very fine water particle mist
- works with demineralised (RO) water
- limited humidification capacity

- innovative
- hygienic



Ultrasonic



12.2.3 Water/pressurised air



12.2.4 Hybrid



**12.3 Conventional 12.3.1 Spray humidifier** 



12.3.2 Wet-cell humidifier



# 13 FANS





### **13 FANS**

# 13.1 Centrifugal fans

- belt-driven
- forward and backward curved blades
- guaranteed high spring efficiency using optimise spring selection
- transport protection
- airofoil blades balanced in accordance with ISO1940 balance class G2,5
- performances in accordance with DIN 24166: diameter 200-280 mm: precision class 2 diameter 315-1000 mm: precision class 1

- high quality
- low noise level
- optimal energy efficiency
- low operating costs



Dual fans



### 13.2 Motors

- high-quality motors
- high efficiency (EFF 1) and improved efficiency (EFF 2)
- optional three thermistors equipped with electric motors
- d.c. motors available
- optional wiring to isolator
- motors in- or outside the air flow

- high quality
- safe
- optimal energy efficiency
- low operating costs



Motor in the air flow



Motor outside the air flow



Run & standby in the air flow



Run & standby outside the air flow Detail, motor outside the air flow






### 13.3 Transmission

- fan assembly complete with a label with the exact data for belt tensioning
- drive selected with Carrier developed software. This software calculates the maximum admissible power on the bearing ring, to ensure a bearing life of L<sub>10h</sub> (standard 25,000 hours for both motor and fan )
- tension base adjustable with one bolt
- number of drive belts: N + 1 = N
- flat belt transmission possible

- high-quality
- made-to-measure
- optimal energy efficiency



Belt tensioning information





# 13.4 Mounting

Various mounting possibilities: single, dual, duplex, run & standby and external motors. There are also five fan discharge positions available as standard.

- the complete fan assembly is a slide-out and vibration-free structure
- flexible connections are always used between fan and pressure wall
- transport protection

- noise reduction
- maintenance and user-friendly
- hygienic



Run & standby motor



Slide-out fan assembly



# 13.5 Options

- Fan belt protection cover
- access screen fan section behind the door
- coated or stainless steel version
- various bearing versions
- pressure measuring points in in-flow cone for flow measurement
- lifting frame
- air distribution screen
- standardised speed controls
- isolator

- safe
- maintenance and user-friendly
- made-to-measure







Air distribution screen



Lifting beam



Access screen

# 13.6 Direct-drive centrifugal fans

- compact installation
- special coupling
- no fan belt erosion (VDI-6022)

- made-to-measure
- high quality
- optimal energy efficiency



# 13.7 Plug fans

- easy to clean
- no fan belt erosion (VDI-6022)

- maintenance and user-friendly
- hygienic

Plug-in fan



### 13.8 Other fans

- mixed flow
- axial

• made-to-measure

### **14 SOUND ATTENUATORS**

- optimised for module system and full height
- absorption as well as resonance damper
- supplied with an erosion-resistant top layer as standard
- removable using a simple removable comb profile
- attenuation values in accordance with ISO 7235-2003
- splitters optionally supplied with face profile
- $\bullet$  other surfaces on request: perforated plate, polyester film
- sound-optimised configuration of gap/splitters possible
- made-to-measure
- acoustic
- maintenance and user-friendly





Comb profile



# **15 DISCHARGE**

- discharge openings in various positions possible:
  - full face
  - half face: top, middle, bottom
  - roof and floor
  - service and non-service side
- marine version

• made-to-measure



Marine discharge plenum

# 16 OUTSIDE INSTALLATION








### **16 OUTSIDE INSTALLATION**

Roof versions: plastic with protruding roof edge, added sloped roof, sun roof with ventilation. Roofs available in various versions.

- stainless steel fixing materials and screws with plastic safety ring
- doors are equipped with an aluminium rain protection profile and storm cord
- possibility for maintenance corridors
- headers can be routed through the floor
- outside air inlet cowl equipped with bird screen
- optional exhaust cowl equipped with aluminium bird screen.
- for several casing parts a lifting frame is available for the lifting of the complete air handling unit in one section
- connection profile for roof covering available
- roofs available in various versions

- corrosion-resistant
- user-friendly
- safe
- made-to-measure



Outdoor air inlet cover



Stainless steel screw with plastic



Storm cord



Plastic roof

# 17 ACCESSORIES



# **17 ACCESSORIES**





Metering console

- View port
  - actuator
  - differential pressure switch
  - frost protection thermostat
  - vibration mats
  - duct connection flange
  - double-skin, acoustic flexible connection
  - differential pressure gauge
  - measuring point
  - frequency controller
  - steam actuator
  - storm cord
  - lighting with switch



Feet







Siphon Light fitting



Actuator





# **18 Control**

- fan capacity control
- constant pressure control
- constant volume control
- frequency control in base casing
- 5 main base casings
  - 1 speed control based on external control signal
  - 2 constant pressure/flow control
  - 3 as above with sequence control, suction fan
  - 4 constant pressure control with sequence control based on air flow
  - 5 adaptive energy-saving speed control for VAV-system
- integrated control box

- user-friendly
- operating safety
- optimal energy efficiency



Integrated control box



# **19 Installations**

### 19.1 Health Care

HEALTH CARE	LOCATION	COUNTRY
Acıbadem – Maslak	İstanbul	Turkey
Dünya Göz Hospital	İstanbul	Turkey
Florance Nightingale Hospital	İstanbul	Turkey
Özel Gaziosmanpaşa Hospital	İstanbul	Turkey
Medicalpark Hospital	Antalya	Turkey
Antalya State Hospital	Antalya	Turkey
Akdeniz University School of Medicine	Antalya	Turkey
Hacettepe University School of Medicine	Ankara	Turkey
Aydın University School of Medicine	Aydın	Turkey
Martia Hospital	Al Marj	Libya



Acıbadem - Maslak, İstanbul



Medicalpark Hospital, Antalya



Dünya Göz Hospital - Etiler, İstanbul



Florence Nightingale Hospital, İstanbul



# **19.2 Shopping Centers**

SHOPPING CENTER	LOCATION	COUNTRY
Ece Ozas Shopping Center	Vilnius	Lithuania
Mega Ikea	Rostov	Russia
Merter M1 Meydan Shopping Center	İstanbul	Turkey
CEPA Shopping Center	Ankara	Turkey
Historia Fatih Shopping Center	İstanbul	Turkey
Ankamall Shopping Center	Ankara	Turkey
Espark Shopping Center	Eskişehir	Turkey
Anse Ev Gereçleri Shopping Center	Ankara	Turkey
Kentpark Shopping Center	Ankara	Turkey
Demirpark Shopping Center	Zonguldak	Turkey
Togliatti Shopping Center	-	Russia
Michurinsky Shopping Center	Moscow	Russia



Cepa Shopping Center, Ankara



Ankamall Shopping Center, Ankara



Mega Ikea - Rostov, Russia



Espark Shopping Center, Eskişehir



## 19.3 Tourist centers, archives, libraries and museums

	LOCATION	COUNTRY
Xanadu Resort Hotel	Muğla	Turkey
Calista Luxury Resort	Antalya	Turkey
Amara Dolce Vita Holiday Village	Antalya	Turkey
Miracle De Luxe Resort	Antalya	Turkey
Crystal Palace Resort Hotel & Spa	Antalya	Turkey
Bursa Historical Çelik Palas Hotel	Bursa	Turkey
Sheraton Hotel	Ankara	Turkey
Susesi Hotel	Antalya	Turkey
World of Wonders Kiriş Resort	Antalya	Turkey
Dedeman Hotel	Zonguldak	Turkey
The Marmara Hotel	Antalya	Turkey
Japanese Anatolia Archeology Museum	Kırşehir	Turkey
Yunkers Museum	Kazan	Tatarstan



Amara Dolce Vita, Antalya



Sheraton Hotel, Ankara



Calista Luxury Resort, Antalya



Susesi Hotel, Antalya



## 19.4 Schools and Universities

SCHOOLS AND UNIVERSITIES	LOCATION	COUNTRY
Middle East Technical University Northern Cyprus	Güzelyurt	N. Cyprus
Dokuz Eylül University	İzmir	Turkey
Muğla University	Muğla	Turkey
İzmir Institute of Technology	İzmir	Turkey
Zonguldak Karaelmas University	Zonguldak	Turkey
Ankara University	Ankara	Turkey
Hacettepe University	Ankara	Turkey
TOBB University of Economics and Technology	Ankara	Turkey
Celal Bayar University	Manisa	Turkey



Celal Bayar University, Manisa



Karaelmas University, Zonguldak



TOBB Ekonomi ve Teknoloji University, Ankara



Muğla University



### **19.5 Industrial Facilities**

INDUSTRIAL FACILITIES	LOCATION	COUNTRY
Bosch Diesel Injector Production Facilities	Bursa	Turkey
Samir Refinery	Muhammediye	Morocco
Altınmarka Food Industry	İstanbul	Turkey
Aselsan	Ankara	Turkey
TAİ (Turkish Aerospace Industries, Inc.)	Ankara	Turkey
Kashagan Oil Search	Atyrau	Kazakhstan

### 19.6 Offices, Bank and Government

	LOCATION	COUNTRY
Akbank Operations Center	İstanbul	Turkey
İstanbul Anatolian Side Court House	İstanbul	Turkey
Şanlıurfa Government House	Şanlıurfa	Turkey
Şanlıurfa Court House	Şanlıurfa	Turkey
The Grand National Assembly Of Turkey	Ankara	Turkey
Ministry of Foreign Affairs	Ankara	Turkey
Constitutional Court Building	Ankara	Turkey
İzmir Court House	İzmir	Turkey



Ministry of Foreign Affairs, Ankara



The Grand National Assembly Of Turkey, Ankara



Constitutional Court Building, Ankara




İzmir Court House



## 19.7 Cultural Centers, Recreation and Theatres

	LOCATION	COUNTRY
Adile Sultan Palace Sakıp Sabancı Kandilli Education & Cultural Center	İstanbul	Turkey
Darüşşafaka Cultural Center	İstanbul	Turkey
Konya Mevlana Cultural Center	Konya	Turkey
Ahmed Adnan Saygun Art Center	İzmir	Turkey
Turkmenistan Theater Building	Ashgabad	Turkmenistan







Ahmed Adnan Saygun Art Center, İzmir

# 19.8 Airports

	LOCATION	COUNTRY
Antalya Airport	Antalya	Turkey
Astana Airport	Astana	Kazakhstan
Kayseri Airport	Kayseri	Turkey
Konya Airport	Konya	Turkey
Denizli Çardak Airport	Denizli	Turkey
Adnan Menderes Airport	İzmir	Turkey



Astana Airport, Kazakhstan



Adnan Menderes Airport, İzmir



## **19.9 Other**


	LOCATION	COUNTRY
Fenerbahçe SK Şükrü Saraçoğlu Stadium	İstanbul	Turkey
Hacettepe University Convention Center	Ankara	Turkey
The Kul Sharif Mosque	-	Tatarstan
Kazan Turkish Consulate	Kazan	Tatarstan
İstinye Park Hillside City Club	İstanbul	Turkey
İnkilap Bookstore	İstanbul	Turkey
Kanaltürk TV Building	İstanbul	Turkey
Akgün Gıda Susurluk Recreation Facilities	Balıkesir	Turkey



Şükrü Saraçoğlu Stadium, İstanbul



The Kul Sharif Mosque, Tatarstan















The company reserves its right to alter its products due to technological developments





ALARKO CARRIER SANAYİ VE TİCARET A.Ş. GOSB-Gebze Organize Sanayi Bölgesi

Şahabettin Bilgisu Cad. 41480 Gebze/Kocaeli/TURKEY

Phone : +90 262 648 60 00 PBX
Telefax : +90 262 648 61 01

web : www.alarko-carrier.com

web : www.alarko-carrier.com.tr
e-mail : info@alarko-carrier.com.tr